





































PIEZOSURGERY® INSERTS QUICK REFERENCE GUIDE

SINUS LIFT TECHNIQUE CRESTAL APPROACH	SINUS LIFT TECHNIQUE LATERAL APPROACH	IMPLANT SITE PREPARATION		MINI DENTAL IMPLANT SITE PREPARATION	RIDGE EXPANSION	PERIOSTEUM PREPARATION	EXTRACTIONS	EXPLANTATION
PIEZO LIFT	STANDARD	STANDARD	OPTIONAL	STANDARD	STANDARD	STANDARD	STANDARD	STANDARD
 PL1	 SLE1	 IM1S	 IM1 AL	 IM1S	 OT7	 PR1	 EX1	 EXP3-R
 PL2	 SLE2	 IM2A	 IM2A-15	 MDI 1.9	 OT4	 PR2	 EX2	 EXP3-L
 PL3	 SLC	 IM3A	 IM2.8A	 MDI 2.2	 OP5		 EX3	 EXP4-R
	 SLO-H	 IM4A	 IM3A-15	 MDI 2.5	OPTIONAL		 PS2	 EXP4-L
	 SLS	 IM2P	 IM3.4A					
SINUS PHYSIOLIFT	OPTIONAL	 IM2P	 IM3A	 IM2P-15	 OT2			
 IM1 SP	 OP3	 IM3P	 IM2P-15	 IM2.8P	 OT7A			
 IM2 SP	 OT1	 IM4P	 IM3P-15	 IM3.4P	 OT7S-4			
 P2-3 SP	 EL1	 OT4			 OT7S-3			
 OT9	 OT5	 P2-3			 OT12			
 CS1	 EL2	 P3-4			 OT12S			
 CS2	 EL3				 OT7-20			
 PIN IM1								
 PIN 2-2.4								
 PROBE SP								



PIEZOSURGERY® INSERTS QUICK REFERENCE GUIDE

BONE BLOCK GRAFTING		BONE CHIP GRAFTING/ BONE MODELING	ENDODONTICS	OSTEOTOMY CLOSE TO NERVES	CORTICOTOMY TECHNIQUE	PERIODONTAL SURGERY		CROWN PREPARATION
STANDARD	OPTIONAL	STANDARD	STANDARD	STANDARD	STANDARD	STANDARD	OPTIONAL	STANDARD
 OT7	 OT6	 OP3	 OP7	 OT1	 OT2	 OP3	 PS1	 DB2
 OP5	 OT7A	 OP1	 PS2	 OT5	 OT7	 OP5	 PS6	
 OT8L	 OT7S-4	OPTIONAL		 EN1	 OT7A	 OP8	 PP10	 TA12D90
 OT8R	 OT7S-3	 OP2	 EN2	 OT5	 OT7S-4	 OP9	 PP11	 TA12D60
	 OT12	 OP3A	 EN3	 OT7S-3	 OT7S-3	 OT13	 PP12	 TA14D120
	 OT12S		 EN4		OPTIONAL		 OP2	 TA14D90
	 OT7-20		OPTIONAL		 OT7-20	 OT14	 OP3A	 TA14D60
			 EN5R			 PP1	 OP4	 TA16D120
			 EN5L			 PS2	 OP6	 TA16D90
			 EN6R				 OP6A	 TA16D60
			 EN6L					
			 OP3				 ICP + IC1	

